



Un 额定电压	=== 880V	=== 880V
Un max. : UL+/UL- *)	=== 1000V	=== 1000V
Un max. : UL/⚡ *)	=== 500V	=== 1000V
塑料外壳式断路器MCCB	四极 4P	四极 4P
应用 Application  负载 Load		
客服电话/ Customer service telephone: 400-150-6060	备注: Remark 1) L+: 电源正极 positive pole of power supply; L-: 电源负极 negative pole of power supply 2)+: 断路器正极 positive pole of MCCB; -: 断路器负极 negative pole of MCCB 3)直流电源通常“L-”接地。“L-” is normally grounded in DC power supply system. 正负电源系统中, 中性极 “M” 接地。neutral pole “M” is grounded in the positive and negative power system *) 250V Max. per pole	